



STYLE 606 DFS

DOUBLE FLOATING SEAL
TENUTA FLOTTANTE DOPPIA
SELLO FLOTANTE DOBLE



 Double floating seal, with multiple springs out of the pumped fluid, extremely compact but able to withstand radial misalignment up to 4°. Equipped with standard pumping ring, the Style 606 DFS seal can be installed in almost every application, even heavy duty pumps, reactors, and mixers.

 Tenuta doppia flottante, con molle multiple fuori dal fluido pompato, estremamente compatta ma in grado di assorbire disassamenti radiali fino a 4°. Senza alcuna parte dentro la cassa stoppa, le particelle solide dei fluidi hanno spazio per circolare e non si depositano sulle facce di tenuta. Questa tenuta è dotata di flangia con connessione per flussaggio e massicce facce di tenuta realizzate in materiali sinterizzati montati su elastomeri flessibili, che agiscono anche da assorbitori di shock, e offre la più grande affidabilità alle condizioni operative più severe.

 Sello flotante doble, con múltiples resortes fuera del fluido bombeado, extremadamente compacto pero capaz de soportar una desalineación radial de hasta 4°. Equipado con un anillo de bombeo estándar, el sello del estilo 606 DFS puede instalarse en casi todas las aplicaciones, incluso en bombas, reactores y mezcladores de trabajo pesado.

TECHNICAL DATA / DATI TECNICI	
Metal parts <i>Parti metalliche</i>	G
Springs <i>Molle</i>	M5
Sliding face <i>Faccia di strisciamento</i>	A - B - Q1 - Q2 - U2
Max pressure <i>Pressione max</i>	Vacuum/Vuoto 700 mm Hg ÷ 3,5 MPa**
Max speed <i>Velocità max</i>	25 m/sec**
O.RING	FKM - EPDM - FFKM - FEPM - TTV
*Upon shaft diameter and speed *Variabile in dipendenza al diametro e alla velocità	
**Depending on materials of sliding faces **Variabile a seconda del materiale delle facce di strisciamento	


SEALTEK s.r.l.
www.sealtek.com
info@sealtek.com

All technical specifications contained in these technical data sheets are intended as guidelines. Sealtek s.r.l. must be informed about the precise conditions of application so that detailed information relating to specific cases can be provided.

06-2024

D	D3	D6	D5	L1	M
30	66	118	97.5	70	14.5
32	66	118	97.5	70	14.5
33	66	118	97.5	70	14.5
35	69	140	99.5	70	14.5
38	74	145	104.5	70	14.5
40	74	145	104.5	70	14.5
42	78	150	110	72	14.5
43	78	150	110	72	14.5
45	78	150	110	72	14.5
48	83.4	155	114.5	72	14.5
50	83.4	155	114.5	72	14.5
53	88	160	119.5	72	14.5
55	88	160	119.5	72	14.5
60	94	165	124.5	72	14.5
65	102	170	129.5	72	14.5
70	109	175	143	75	21
75	121	180	155	75	21
80	131	185	165	75	21
85	134	190	168	75	21
90	142	195	176	75	21
95	142	200	176	75	21
100	148	210	182	75	21